




OPERATING INSTRUCTION

NL4MMX | speakON Adapter



The new **SECURE LOCK** feature of the NL4MM adapter enables to double lock the NL4FC cable connector on one side.

A Connecting:

The NL4MM **LOCKING RING** has to be on the back position as shown.

(☞ UNLOCKED ☞ = visible)

B Insert the cable connector NL4FC ① and turn clockwise ② to lock (1st lock).

C Slide the NL4MM ring to the **LOCK** position (2nd lock).

Release:

A Slide the NL4MM ring to **UNLOCK** position.

B To separate the NL4FC: Pull latch ① and turn counterclockwise ②.

NEUTRIK AG LI T: +423 / 237 24 24 F: +423 / 232 53 93
NEUTRIK Zürich AG CH T: +41 44 / 736 5010 F: +41 44 / 736 5011
NEUTRIK USA Inc. USA T: +1 732 / 901 9488 F: +1 732 / 901 9608
NEUTRIK (UK) Ltd. UK T: +44 1983 / 811 441 F: +44 1983 / 811 439

NEUTRIK Vertriebs GmbH DE/NL/AT/DK T: +49 8131 / 280 890 F: +49 8131 / 280 830
NEUTRIK France FR T: +33 1 / 4131 6750 F: +33 1 / 4131 0511
NEUTRIK Tokyo Ltd. JP T: +81 3 / 3663 4733 F: +81 3 / 3663 4796
NEUTRIK Hong Kong Ltd. HK T: +852 / 2687 6055 F: +852 / 2687 6052

Draft. Nr.: BDA 112 / 3102M1151 | Update: 21.04.2009 | Data subject to change without prior notice. ©2009 NEUTRIK®. ALL RIGHTS RESERVED.

www.neutrik.com

NEUTRIK